

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

Киргизия (996)312-96-26-47

Россия (495)268-04-70

Казахстан (772)734-952-31

<https://micronic.nt-rt.ru/> || moc@nt-rt.ru

MICRONIC SIDE BARCODE READERS



The Micronic Side Barcode Reader can be mounted on the side of a scanner to read the 1D barcode of a rack. When mounted, the Micronic Code Reader Software can read both the 1D rack barcode and 2D tube codes simultaneously. The reader is available as an option for the following whole rack scanners: the Micronic Rack Reader DR710, DR700 and DR505. The 1D reader is easy to use and avoids manual operations. Additionally, the Side Barcode Reader can be mounted on either the long side or the short side of the Rack Readers, improving compatibility.

MICRONIC CODE READERS

To enable fast, accurate and efficient sample identification, Micronic offers an extensive code reader range which consists of whole rack and single tube readers. The high-end DR700 and DR710 Rack Readers feature deep focus image technology (CCD imaging technology) ensuring the highest accuracy 2D code reading, and an anti-frost system so that tube codes from even frozen samples can be read. The DR700 has a passive anti-frost system, whereas the DR710 has an active anti-frost system. The DR700 and DR710 have a scan time of approximately 7 seconds. To read 1D rack barcodes simultaneously, the Side Barcode Reader is available.

The Micronic Rack Reader DR505 is a small benchtop solution that can read 2D codes quickly and cost effective within seconds. The compact reader is built for high throughput and automated systems. The DR505 has a passive anti-frost system, which enables users to read racks filled with 2D codes tubes straight from the freezer. All Micronic Rack Readers are standard supplied with Micronic Code Reader Software to ensure an optimal performance.

Article Number	Description	Unit Size
MP35240	Micronic Side Barcode Reader for DR500 line	1 unit
MP35250	Micronic Side Barcode Reader for DR700 line	1 unit