

Архангельск (8182)63-90-72  
Астана (7172)727-132  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89  
Иваново (4932)77-34-06

Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16

Пермь (342)205-81-47  
Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35  
Тверь (4822)63-31-35  
Томск (3822)98-41-53  
Тула (4872)74-02-29  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Ярославль (4852)69-52-93

Киргизия (996)312-96-26-47

Россия (495)268-04-70

Казахстан (772)734-952-31

<https://micronic.nt-rt.ru/> || [moc@nt-rt.ru](mailto:moc@nt-rt.ru)

# MICRONIC SCREW CAP RECAPPER CS500



The Micronic Screw Cap Recapper CS500 line is developed in conjunction with several leading laboratories. The handheld device offers users the ability to cap, decap or recap a row of **8 (CS500 model), 6 (CS510 model) or 4 (CS520 model) tubes** in less than 5 seconds – 10 times faster than by hand! Thereby, minimizing sample evaporation and significantly improving productivity. In addition, the Screw Cap Recapper ensures each screw cap is reproducibly tightened securely and uniformly. The Screw Cap Recapper CS500 requires no battery charging and is therefore always available for use. The reliable and robust Micronic Screw Cap Recapper CS500 comes with a 1-year warranty!

Micronic offers the CS500 line for use with other brands of tubes and caps (Thermo, FluidX and LVL). This means that if you use sample storage tubes or caps from another brand, it is still possible to benefit from the wide range of qualities our recapper offers. As a usefull add-one, Micronic offers the **Docking Station for the CS500 line**, to assure a consistent (de-)capping action. Inquire now about the attractive combi-deal: the Docking Station together with the Screw Cap Recapper.

## CAPPING & DECAPPING SYSTEMS

To enhance and accelerate the capping and decapping process, the Micronic (De)Capping line provides you with several options. The Screw Cap Recapper **CS100** is developed to improve the manual (de)capping of tubes. The cost-effective tools are set to a precise torque value and stop turning when a perfect seal is established, ensuring an optimal sealing performance. Developed in conjunction with several leading laboratories, the Screw Cap Recapper **CS500** offers the ability to cap, decap or recap a row of tubes in less than 5 seconds and a whole rack in only 1 minute. This is 10 times faster than by hand and improves productivity. The automated Screw Cap Recapper **CS700** is “must-have” equipment for higher throughput users. The devices are user-friendly and extremely durable and reliable and cap entire racks in 30 seconds.

## Parameter Screw Cap Recapper CS500

Compatibility	ANSI/SLAS standard 96-format racks
Cycle time	Less than 5 seconds per row
Dimensions	17.8 x 16.1 x 71.0 cm / 7.01 x 6.34 x 27.95 in
Voltage	15 - 230V