

Архангельск (8182)63-90-72  
Астана (7172)727-132  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89  
Иваново (4932)77-34-06

Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16

Пермь (342)205-81-47  
Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35  
Тверь (4822)63-31-35  
Томск (3822)98-41-53  
Тула (4872)74-02-29  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Ярославль (4852)69-52-93

Киргизия (996)312-96-26-47

Россия (495)268-04-70

Казахстан (772)734-952-31

<https://micronic.nt-rt.ru/> || [moc@nt-rt.ru](mailto:moc@nt-rt.ru)

# MICRONIC SCREW CAP RECAPPER CS100



The Micronic Screw Cap Recapper CS100 line is developed to improve the manual (de)capping of tubes. The manual Recappers are available for **96- (CS100 model), 48- (CS110 model) or 24-well (CS120 model) format tubes** with internal thread or external thread. The cost-effective tools (non battery powered) are set to a precise torque value and stop turning when a perfect seal is established, ensuring an optimal sealing performance.

This versatile tool is only available at Micronic and can be made compatible with tubes from other brands. Contact us with your request.

## CAPPING & DECAPPING SYSTEMS

Micronic offers a range of products to make the capping and decapping process more efficient. For the manual (de)capping of Screw Caps, there is one option available. The Screw Cap Recapper CS100 is set to a precise torque value and stops turning when the perfect seal is established.

Developed in conjunction with several leading laboratories, the Screw Cap Recapper **CS500** offers the ability to cap, decap or recap a row of tubes in less than 5 seconds and a whole rack in only 1 minute. This is 10 times faster than by hand and improves productivity. The automated Screw Cap Recapper **CS700** is “must-have” equipment for higher throughput users. The devices are user-friendly and extremely durable and reliable and cap entire racks in 30 seconds.

### Parameter Screw Cap Recapper CS100

|               |                                  |
|---------------|----------------------------------|
| Compatibility | 96-, 48- or 24-well format tubes |
| Cycle time    | Seconds                          |
| Dimensions    | 13.0 x 1.9 cm / 5.11 x 1.18 in   |