

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

Киргизия (996)312-96-26-47

Россия (495)268-04-70

Казахстан (772)734-952-31

<https://micronic.nt-rt.ru/> || moc@nt-rt.ru

MICRONIC PUSH CAP CAPPER CP400



The Micronic Push Cap Capper CP400 offers a cost effective way of applying uniform pressure to push caps in an entire 96 tubes rack in only a single action. Built to meet the varying needs of different users, the CP400 can seal full or partially full racks with the complete range of Micronic TPE or EVA style capmats, capbands and capclusters. The capper is also compatible with other brands of storage tubes and racks.

The manual capper is able to repeatably and reliably securely cap tubes (up to 1.40 ml) in all ANSI /SLAS format racks up to a maximum height of 48mm. To ensure optimum results an adapter matched to your specific rack type and tube height is supplied.

CAPPING & DECAPPING SYSTEMS

Micronic offers a range of products to make the capping and decapping process of tubes more efficient. For the decapping of Push Caps, the Micronic Manual Push Cap Decappers are developed. The range includes the Manual Decapper-1, which is made of high quality plastic, and designed to remove a single Push Cap. The Manual Decapper-8 is also made of high quality plastic and removes Push Caps in a row of eight. The Manual Decapper-8 Aluminum removes individual Push Caps in a row of eight from frozen tubes. All manual decappers provide a convenient and fast removal of the TPE Push Caps.

The Push Cap Capper CP400 can apply uniform pressure to Push Caps in an entire 96 tubes rack in only a single action. This device is able to seal full racks or partially full racks with the complete range of Micronic TPE or EVA style Capmats, Capbands and Capclusters. The Capper is also compatible with other brands of storage tubes and racks.

Parameter

Push Cap Capper CP400

Rack compatibility	ANSI / SLAS standard 96-format
Maximum rack height	48mm
Push cap compatibility	TPE or EVA
Dimensions	262 x 185 x 164 mm
Weight	7 Kg / 15 lbs